

FF7LBIMED2ADA



32.38" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant auto defrost medical/scientific all-refrigerator with front control panel equipped with a digital thermostat and NIST calibrated thermometer/alarm; includes front lock, hospital grade cord, and internal fan

Highlights:

User-friendly front control panel keeps the thermostat and alarm in reach without having to open the door

Specially designed and featured to meet the CDC and VFC's guidelines for safe vaccine storage

Flexible design allows built-in or freestanding use in 24" wide spaces

Product Features:

Reliable temperature stability	Designed and engineered to store vaccines and other sensitive materials under stable temperature conditions
ADA compliant design	Sized at 32" high to allow installation under lower ADA compliant counters
Built-in capable	Front-breathing system allows the unit to be used built-in
Digital thermostat	Digital microprocessor for easy and precise temperature management, with all controls externally located for added convenience
High/low temperature alarm	Audible alarm sounds if the interior temperature rises or falls out of set range
NIST calibrated temperature display	Alarm includes continuous NIST calibrated display of the current interior and high/low temperature, and can be switched from Celsius to Fahrenheit at the touch of a button
Buffered temperature probe	Thermometer probe is encased in a glycol-filled bottle and stored in a fixed box on the center shelf. This is the ideal way to produce temperature readings closest to stored contents, as recommended by the CDC and VFC's guidelines
Factory installed lock	Keyed lock conveniently located towards the top of the door for added security (2 keys included)
Automatic defrost	Reduced maintenance with auto defrost system

FF7LBIMED2ADA Specifications:

Overview	
Height of Cabinet	32.0" (81 cm)
Height to Hinge Cap	32.38" (82 cm)
Width	23.63" (60 cm)
Depth	23.5" (60 cm)
Depth with Handle	25.0" (64 cm)
Depth with door at 90°	45.75" (116 cm)
Capacity	5.5 cu.ft. (156 L)
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	90.0 lbs. (41 kg)
Shipping Weight	110.0 lbs. (50 kg)
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Temperature Range	2° to 8°C
Dimensions	
Interior Height	26.25" (67 cm)
Interior Width	21.0" (53 cm)
Interior Depth	18.0" (46 cm)

Compressor Step Height	5.5" (14 cm)
Compressor Step Width	21.0" (53 cm)
Compressor Step Depth	5.5" (14 cm)

