



ULTRA-SIDEWINDER

TECHNICAL SPECIFICATIONS

3-FOOT SYSTEMS		1-FOOT EXTENSIONS	
<u>Part Number</u>	<u>Color</u>	<u>Part Number</u>	<u>Color</u>
1800	Black & Yellow	1801	Black & Yellow
1802	Black	1803	Black
1804	Brown	1805	Brown
1806	Gray	1807	Gray
24-FOOT SYSTEM			
Part Number 1820		Black & Yellow	

- **Construction:** Injection-molded acrylonitrile butadiene styrene (ABS) plastic and injection-molded Santoprene™ vulcanized rubber tabs.
- **Overall Dimensions:**
3-Foot Systems – 40" long x 3" wide x 3/4" tall (1062mm x 76mm x 19mm); 1.5 lbs (0.7kg)
1-Foot Extensions – 12" long x 3" wide x 3/4" tall (394mm x 76mm x 19mm); 0.5 lbs (0.2kg)
24-Foot Systems – 292" long x 3" wide x 3/4" tall (7417mm x 76mm x 19mm); 12 lbs (5.5kg)
- **Internal channel opening:** 3/4" (19mm) wide x 3/8" (9.5mm) high.
- **Maximum Weight Capacity:** 2,000 lbs. / sq. in. (907 kg)
- Articulating piece connections make it possible to turn unit around obstructions or to create a change in direction. Maximum turn per segment is approximately 8 - 10 degrees.
- Assembled units can be coiled with the cord in place, creating a 2-ft (approximately) diameter coil for moving and storage.
- Systems are purchased in 3-Foot or 24-foot lengths (including two end caps) with optional 1-Foot Extensions available. Segments can be removed to create custom lengths in 1-1/2" increments.
- Modular design allows for easy reconfiguration or repair, even with the cable or cord in place.
- Unit is designed for office and light-industrial use and is designed to be run on flat, stable surface and not intended to span gaps, holes, or trenches with any weight load.
- **Operating temperatures:** -40 °F to 120 °F (-40 °C to 49 °C)