

# MASTER<sup>®</sup>


## MASTER MAC-30D 30" High Capacity Direct-Drive Barrel Fan— 5500 CFM, 1/3 HP, 120 Volt



- DURABLE—great for garages, barns, or workshops, or outside events
- POWERFUL—steel construction
- INDUSTRY-LEADING—high airflow for up to 5500 CFM
- Machined industrial motor, steel-coated safety grille, built-in handle, and more
- 1-year limited warranty

### Product Description

Get ready for an unrivaled cooling solution like no other. The MASTER 30" High Capacity Direct-Drive Barrel Fan will blow you away with the massive amount of air it moves and its quiet, direct-drive operation. When you need to save on A/C and cool a giant indoor or outdoor space, this fan has you covered. With rock-solid wheels for portability and the durable steel construction you demand, you know you're getting the best. This is a true workhorse air circulator. MASTER – built for power.



## Features and Benefits

- Great for garages, barns, or workshops, or outside events
- Powerful steel construction
- High airflow for up to 5500 CFM
- 1/3 HP fully enclosed, industrial motor
- Built-in handle
- Steel-coated safety grille
- 2 variable speed settings
- Rock-solid wheels
- 1-year limited warranty

## Key Specs

<b>Model Number</b>	MAC-30D
---------------------	---------

<b>Brand</b>	MASTER
--------------	--------

<b>Warranty</b>	1-year limited warranty
-----------------	-------------------------

<b>Net Weight (lb.)</b>	36
-------------------------	----

<b>Air Flow (CFM)</b>	4500 / 5500
-----------------------	-------------

<b>Motor Size (HP)</b>	1/3
------------------------	-----

<b>Variable Speed</b>	Yes
-----------------------	-----

<b>Volts</b>	120
--------------	-----

<b>Amps</b>	2.5
-------------	-----

<b>Dimensions (L x W x H) (in.)</b>	33 x 11.5 x 33
-------------------------------------	----------------