



**MCR
SAFETY**

Stratos

Safety Glasses

Value Series

Specification Sheet

PRODUCT DESCRIPTION:

The Stratos® features a one piece polycarbonate lens and a stylish wrap-around design that offers the user a wide area of protection. Integral side shields offer protection from particles entering the eyewear from the sides. The Stratos® provides an exceptional wide angle of unrestricted vision allowing you to safely assess your environment. The molded-in nose bridge comfortably fits a wide variety of faces. The Stratos® features a stylish wrap-around design and one piece polycarbonate lens with integral sideshields that filters out 99.9 percent of UV radiation. The lightweight frame provides added comfort and balance. Available in four frame and two lens tint options.



FEATURES:

- Cost efficient single lens design
- Spatula temple with extendable adjustment
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays

TECHNICAL DATA FOR: SS010

Brand Series Category	MCR Safety Stratos Safety Glasses	Frame Material Packaging	Nylon White Inner Box
Case Pack	144 pair	MIL - PRF - 31013	N/A
Case Dimensions	22.047 x 14.173 x 12.992	ANSI Z87+	Yes
Case Weight	15.597 oz.	AS/NZS 1337.1	N/A
Made In	Taiwan	CE EN166	N/A

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
SS010	Clear	Uncoated	No	90	Black	Black	N/A
SS110	Clear	Duramass Hard Coat	Yes	90	Black	Black	N/A
SS110AF	Clear	Duramass Anti-Fog	Yes	90	Black	Black	N/A
SS112	Gray	Duramass Hard Coat	Yes	13	Black	Black	N/A



MCR
SAFETY

Stratos

Safety Glasses

Value Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
SS120	Clear	Duramass Hard Coat	Yes	90	Blue	Blue	N/A
SS130	Clear	Duramass Hard Coat	Yes	90	Blue	Red / White	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved