


# DIRT DAWGS



## LAST LONGER, USE FEWER

Take a bite out of your disposable respirator costs with Dirt Dawgs®! The Dura-Mesh® shell, exclusive to Moldex®, protects the filter media so it stays cleaner-looking longer. Plus, it resists collapsing, even in heat and humidity so the respirator holds its shape longer. The result is fewer respirators used and lower costs. Meets heat and flame resistance in accordance with ANSI/ISEA 110-2003 Section 7.11.1.

## EASY FIT, MORE COMFORT

The molded nose bridge provides the wearer an easy comfortable fit. There's no metal noseband to adjust, and the seal is maintained without pressure points.

The Softspun® lining is soft to the touch, which means workers won't mind wearing it for an entire shift.

## MOLDEX TECHNICAL SUPPORT

Moldex provides technical assistance including help with fittesting, a Train-the-Trainer Program, a manual on How To Set-Up Your Respiratory Protection Program, plus a Toll-Free Technical Help line. Just call 800/421-0668 ext. 550 or 310/837-6500 ext. 512/550.

## FEATURES

- 100% PVC-Free.
- Durability at an affordable price.
- Dura-Mesh® shell resists collapsing in heat and humidity.
- Molded nose bridge seals easily without a metal noseband.
- Facepiece is naturally contoured without pressure points.
- Straps are securely attached so they don't break at the seal.
- Softspun® lining for increased comfort and durability.
- NIOSH certified to have a filter efficiency of 95% or greater for non-oil based particulates.
- Meets heat and flame resistance in accordance with ANSI/ISEA 110-2003 Section 7.11.1.
- Certified under 42CFR84.



## USE AGAINST:

1. Particulate aerosols free of oil.

## DO NOT USE AGAINST:

1. Concentrations of contaminants which are unknown, or are immediately dangerous to life or health.
2. Concentrations of particulates which exceed the maximum use concentration or 10 times the OSHA Permissible Exposure Limit, whichever is lower.
3. Gases, vapors, asbestos, paint spray, sandblasting or particulate materials which generate harmful vapors.
4. Oil-based mists.

## RESTRICTIONS

1. This respirator does not supply oxygen and must not be used in atmospheres containing less than 19.5% oxygen.
2. Do not remain in contaminated area if any physical distress occurs, for example breathing difficulty, dizziness or nausea.
3. Leave contaminated area and replace respirator if it is damaged, distorted, a proper fit can not be obtained or breathing becomes difficult.
4. Prior to each use, carefully inspect the entire respirator, including filter media and strap attachment area for tears and damage. Staple or strap attachment perforations do not effect NIOSH approval.
5. Do not alter, modify, or abuse this respirator.
6. Store unused respirators in box/bag in a clean, dry, non-contaminated area.
7. Dispose of respirator according to your employer's policy and local regulations.
8. Dispose no later than thirty days after first use.
9. Use respirator before the "use by" expiration date printed on box/bag.
10. If used for welding, wear appropriate eye and face protection.

## TECHNICAL SERVICE HELP LINE

For technical assistance call Moldex Technical Service Department, 310/837-6500 or 800/421-0668 ext. 512/550.

### MOLDEX-METRIC, INC.

10111 W. Jefferson Blvd. Culver City, CA 90232  
TEL: 800/421-0668 or 310/837-6500 FAX 310/837-9563  
www.moldex.com e-mail: sales@moldex.com

### CANADIAN CUSTOMER SERVICE

TEL: 310-837-6500, Ext. 517  
FAX: 310-837-9563

Moldex, Ideas that wear well, Dura-Mesh and Softspun are registered trademarks. The mesh design is a trademark of Moldex/Metric, Inc. U.S. Patents #D285,374 and #4,850,347 Made in the U.S.A. 9702-764 REV C 02/09

TC-	Protection <sup>1</sup>	Respirator			Cautions and Limitations <sup>2</sup>
		1200N95	1201N95	1207N95	
84A-3167	N95	X	X	X	A B C J M N O P

THESE RESPIRATORS ARE APPROVED ONLY IN THE FOLLOWING CONFIGURATIONS:

1. PROTECTION  
N95-Particulate Filter (95% filter efficiency level) effective against particulate aerosols free of oil; time use restrictions may apply

2. CAUTIONS AND LIMITATIONS  
A- Not for use in atmospheres containing less than 19.5 percent oxygen.  
B- Not for use in atmospheres immediately dangerous to life or health.  
C- Do not exceed maximum use concentrations established by regulatory standards.  
D- Failure to properly use and maintain this product could result in injury or death.  
E- All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA, and other applicable regulations.  
F- Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configuration as specified by the manufacturer.  
G- Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.  
P- NIOSH does not evaluate respirators as surgical masks.

## PACKAGING

20 Respirators per Box	1200N95	Medium/Large
18 Boxes per Case	1201N95	Small
	1207N95	Low Profile

## LIMITED WARRANTY IMPORTANT NOTICE TO PURCHASER

This limited warranty is made in lieu of the warranties of merchantability, fitness for particular purposes and all other warranties, express or implied. There are no other warranties which extend beyond the description on the face hereof. The physical standards and specifications of Moldex will be met by products sold. **Exclusive Remedies:** damages for the breach of this limited warranty are limited to the replacement of such quantity of Moldex products proved to be defectively manufactured. Except as provided above, Moldex shall not be liable or responsible for any loss, damages, or liability, direct, indirect, incidental, special or consequential, arising out of a sale, use or misuse, or the inability to use products by the user.



## WARNING TO USER

1. Follow all instructions and warnings on the use of this respirator and wear during all times of exposure. Failure to do so will reduce respirator effectiveness, wearer protection and may result in sickness or death.
2. Before use, the user must first be trained by the employer in proper respirator use, in accordance with applicable safety and health standards, for the contaminant and exposure level in the assigned work area.
3. The particulates and other contaminants which can be dangerous to your health include those which you cannot see, taste, or smell.
4. This product has not been sold with warnings or use instructions for personnel involved in healthcare or related situations, where there may be the possibility of contact with disease or biological hazards. If you are considering such uses, first call the Moldex Technical Service Dept., 310/837-6500 or 800/421-0668 ext. 512/550.

## DISTRIBUTED BY:



Printed on Recycled Paper



**MOLDEX**  
Ideas that wear well.