

MOLDEX[®]
Ideas that wear well.™

R95 Series

PARTICULATE RESPIRATORS

HandyStrap[®], with buckle, allows mask to hang around neck when not in use.

Ventex[®] valve lets the hot air out faster so workers breathe easier and stay cooler.

R95 protection against both oil and non-oil based particulate aerosols.

Added sorbent helps filter out nuisance levels of ozone/organic vapors (2840/1R95) or acid gas irritants (2940/1R95).

Soft foam nose flange for added comfort and no pressure points.


Dura-Mesh[®] shell resists collapsing in heat and humidity.

Flame retardants added to decrease flammability of shell.

2740R95 – Medium/Large; 2741R95 – Small

2840R95 – Medium/Large; 2841R95 – Small, Plus Ozone/Organic Vapor Relief

2940R95 – Medium/Large; 2941R95 – Small, Plus Acid Gas Relief



R95 OIL & NON-OIL PROTECTION.

NIOSH certified under 42CFR84 regulations to have a filter efficiency level of 95% or greater against oil and non-oil based particulate aerosols up to 10 X PEL. Added carbon layer helps relieve workers of nuisance levels (less than OSHA Permissible Exposure Limit) of ozone and organic vapor odors (2840/1R95) or acid gas irritants (2940/1R95).

HANGS LOOSE.

HandyStrap allows mask to conveniently hang around neck. So it's always ready for use. And during wear the stretch cloth strap is more comfortable and cooler.

VENT HOT AIR, STAY COOLER.

Exclusive Ventex valve lets the hot air out faster. So breathing resistance is reduced and workers stay cooler.

DURA-MESH SHELL LASTS LONGER.

The Dura-Mesh shell protects the filter media so it stays cleaner looking longer. Plus it resists collapsing, even in heat and humidity. So the respirator holds its shape longer. The result is fewer respirators used and lower costs.

MOLDEX TECHNICAL SERVICE.

Moldex provides technical assistance including help with fit testing, a *Train-the-Trainer Program*, *How To Set-Up Your Respiratory Protection Program* plus a Toll-Free Technical Help line. Just call 800/421-0668 ext. 550, or 310-837-6500 ext. 550.

R95 PARTICULATE RESPIRATORS

APPLICATIONS:

⚠ WARNING TO USER:

Follow all instructions and warnings on the use of this respirator and wear during all times of exposure. Failure to do so will reduce respirator effectiveness, wearer protection and may result in sickness or death.

Before use, the user must first be trained by the employer in proper respirator use, in accordance with applicable safety and health standards, for the contaminant and exposure level in the assigned work area.

The particulates and other contaminants which can be dangerous to your health include those which you cannot see, taste, or smell.

This product has not been sold with warnings or use instructions for personnel involved in healthcare or related situations, where there may be the possibility of contact with disease or biological hazards. If you are considering such uses, first call the Moldex Technical Service Dept., 310/837-6500 ext. 550, or 800/421-0668 ext. 550.

USE AGAINST:

1. Oil and non-oil particulate aerosols.
2. For 2840/1R95 only, nuisance levels (less than OSHA Permissible Exposure Limits) of Organic Vapor Odors and/or Ozone.
3. For 2940/1R95 only, nuisance levels (less than OSHA Permissible Exposure Limits) of Acid Gas Irritants.

DO NOT USE AGAINST:

1. Concentrations of contaminants which are unknown or are immediately dangerous to life or health.
2. Concentrations of particulates which exceed the maximum use concentration or 10 times the OSHA Permissible Exposure Limit, whichever is lower.
3. Gases, vapors, asbestos, paint spray, sandblasting or particulate materials which generate harmful vapors. These respirators are **NOT** approved for any vapors or gases, so when 2840/1R95 is used against Organic Vapor Odors and/or Ozone or 2940/1R95 is used against Acid Gas Irritants, do not exceed the OSHA Permissible Exposure Limit.
4. Oil-based particulate aerosols for longer than 8 hours after first use.

RESTRICTIONS:

1. This respirator does not supply oxygen and must not be used in atmospheres containing less than 19.5% oxygen.
2. Do not remain in contaminated area if any physical distress occurs, for example breathing difficulty, dizziness or nausea.
3. Leave contaminated area and replace respirator if it is damaged, distorted, a proper fit can not be obtained or breathing becomes difficult.
4. Do not alter, modify, or abuse this respirator.
5. Store unused respirators in sealed bag in a clean, dry, non-contaminated area.
6. Dispose of respirator according to your employer's policy and local regulations.
7. Where oil mists are present, dispose no later than eight hours after first use.
8. Dispose no later than thirty days after first use.
9. Use respirator before the "use by" expiration date printed on box.

MOLDEX-METRIC, INC.

10111 W. Jefferson Blvd.
Culver City, CA 90232
800/421-0668 310/837-6500
FAX 310/837-9563

www.moldex.com e-mail: sales@moldex.com


Moldex, HandyStrap, Ventex and Dura-Mesh are registered trademarks. U.S. Patents #D285,374, #D389,239, #D387,015, #4,384,577, #4,850,347, #5,149,468, #5,970,585, # 6,047,698. Made in the U.S.A. 9701-759 REV F 4/05




R95 Series

PARTICULATE RESPIRATORS

APPROVAL



**MOLDEX/METRIC
INCORPORATED**
CULVER CITY, CALIFORNIA, U.S.A.



| THIS RESPIRATOR IS APPROVED ONLY IN THE FOLLOWING CONFIGURATION: | | | | | | | |
|--|------------|--------------------------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------------|
| TC | PROTECTION | RESPIRATOR | | | | | CAUTIONS AND LIMITATIONS ² |
| | | 2 7 4 0 D R 9 5 | 2 7 4 1 R 9 5 | 2 7 4 1 R 9 5 | 2 7 4 1 R 9 5 | 2 7 4 1 R 9 5 | |
| 84A-3231 | R95 | X | X | | | | ABCJMNOP |
| 84A-3231 | R95 | | | X | X | | ABCJMNOP |
| 84A-3174 | R95 | | | | X | X | ABCJMNOP |

1. Protection
R95-Particulate Filter (95% filter efficiency level) effective against all particulate aerosols; time use restrictions may apply.

2. Cautions and Limitations
A- Not for use in atmospheres containing less than 19.5 percent oxygen.
B- Not for use in atmospheres immediately dangerous to life or health.
C- Do not exceed maximum use concentrations established by regulatory standards.
J- Failure to properly use and maintain this product could result in injury or death.
M- All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA, and other applicable regulations.
N- Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configuration as specified by the manufacturer.
O- Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.
P- NIOSH does not evaluate respirators as surgical masks.

TECHNICAL HELP LINE

For information, technical assistance, and training materials call 800/421-0668 ext. 550, or 310/837-6500 ext. 550.

PACKAGING

10 Respirators per box
10 Boxes per case
100 Respirators per case

LIMITED WARRANTY

IMPORTANT NOTICE TO PURCHASER

This limited warranty is made in lieu of the warranties of merchantability, fitness for particular purposes and all other warranties, express or implied. There are no other warranties which extend beyond the description on the face hereof. The physical standards and specifications of Moldex will be met by products sold. **Exclusive Remedies:** damages for the breach of this limited warranty are limited to the replacement of such quantity of Moldex products proved to be defectively manufactured. Except as provided above, Moldex shall not be liable or responsible for any loss, damage, or liability, direct, indirect, incidental, special, or consequential, arising out of sale, use, or misuse, or the inability to use products by the user.

DISTRIBUTED BY:

In Canada:

Moldex-Metric, Inc.
The Ralston/CanSafe Group
P.O. Box 263
Fergus, Ontario N1M 2W8
PHONE 800/267-1611 FAX 519/787-3732