



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



72000 Series PVC Adjustable General Purpose Drain PVC Barrel With 6" Round Grate



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose floor drains are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Grate Finish	Part Number
	3 or 4 in. Pipe Fit	PVC	Stainless	72117
	3 or 4 in. Pipe Fit	PVC	Brass	72127
	3 or 4 in. Pipe Fit	PVC	Nickel	72157
	3 or 4 in. Pipe Fit	PVC	Chrome	72187
	4 in. Pipe Fit	PVC	Stainless	72118
	4 in. Pipe Fit	PVC	Brass	72128
	4 in. Pipe Fit	PVC	Nickel	72158
	4 in. Pipe Fit	PVC	Chrome	72188
	4 in. Hub Fit	PVC	Stainless	72119
	4 in. Hub Fit	PVC	Brass	72129
	4 in. Hub Fit	PVC	Nickel	72159
	4 in. Hub Fit	PVC	Chrome	72189

Primer tap knock-out option available on 3" or 4" Pipe Fit and 4" Pipe Fit bases. 4" Hub Fit base does not include primer tap.

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.00 – 2.50 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.00 – 2.50 in.	4 in. Pipe
4 in.	2.00 in.	1.00 – 2.50 in.	4 in. Hub

Finish	Grate Properties	
	Open Area	Load*
300 Series Stainless Steel	7.10 in. ²	Light
Brass	7.10 in. ²	Medium
Nickel	7.10 in. ²	Medium
Chrome	7.10 in. ²	Medium

*Load is defined by ASME A112.21.1M.
Light Duty – Safe live load under 2000 lbs.
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



82000 Series ABS Adjustable General Purpose Drain PVC Barrel With 6" Round Grate



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose floor drains are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Grate Finish	Part Number
	3 or 4 in. Pipe Fit	ABS	Stainless	82117
	3 or 4 in. Pipe Fit	ABS	Brass	82127
	3 or 4 in. Pipe Fit	ABS	Nickel	82157
	3 or 4 in. Pipe Fit	ABS	Chrome	82187
	4 in. Pipe Fit	ABS	Stainless	82118
	4 in. Pipe Fit	ABS	Brass	82128
	4 in. Pipe Fit	ABS	Nickel	82158
	4 in. Pipe Fit	ABS	Chrome	82188
	4 in. Hub Fit	ABS	Stainless	82119
	4 in. Hub Fit	ABS	Brass	82129
	4 in. Hub Fit	ABS	Nickel	82159
	4 in. Hub Fit	ABS	Chrome	82189

Primer tap knock-out option available on 3" or 4" Pipe Fit and 4" Pipe Fit bases. 4" Hub Fit base does not include primer tap.

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.00 – 2.50 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.00 – 2.50 in.	4 in. Pipe
4 in.	2.00 in.	1.00 – 2.50 in.	4 in. Hub

Finish	Grate Properties	
	Open Area	Load*
300 Series Stainless Steel	7.10 in. ²	Light
Brass	7.10 in. ²	Medium
Nickel	7.10 in. ²	Medium
Chrome	7.10 in. ²	Medium

*Load is defined by ASME A112.21.1M.

Light Duty – Safe live load under 2000 lbs.

Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.