



ULTRATECH
INTERNATIONAL, INC.

Ultra-Containment Berm® Modular Model (Gorilla Berm)

Versatile spill containment that can be reused and easily modified

KEY FEATURES AND BENEFITS

- + Modular construction allows containment areas of any size to be configured.
- + Polymer-coated foam support blocks (6' lengths) provide structure to sidewalls - can be driven over repeatedly without damage.
- + Standard materials include 38 mil and 54 mil slip resistant PVC. Other materials available upon request.

SIDEWALLS

- + Triangular-shaped, polymer-coated foam support blocks (72"L x 18"W x 6"H) are used with rebar (not included) to provide sidewall structure.
- + Molded-in slots in top of foam blocks hold rebar - secures material in place.
- + No set-up required once Berm has been positioned in the field.

COMPLIANCE

- + EPA 40 CFR 264.175 Containment of Containers Containing Free Liquid.
- + SPPC - Spill Prevention, Control and Countermeasure Act





Part#	Dimensions ft. (m) Wall Height: 6 in. (152 mm)	Number of Modular Walls	Containment Capacity gal (L)	Weight lbs. (kg)
8740	6 x 8 (1.8 x 2.4)	6	175 (662.4)	98 (44.5)
8741	12 x 12 (3.7 x 3.7)	10	600 (2271.2)	183 (83)
8742	12 x 20 (3.7 x 6.1)	12	875 (3,312.2)	226 (102.5)
8743	12 x 30 (3.7 x 9.1)	16	1400 (5,299.6)	300 (136.1)
8744	12 x 40 (3.7 x 12.2)	20	1950 (7,381.6)	397 (180.1)
8745	12 x 50 (3.7 x 15.2)	22	2200 (8,327.9)	439 (199.1)
8746	12 x 60 (3.7 x 18.3)	26	2750 (10,409.9)	505 (229.1)
8747	20 x 50 (6.1 x 15.2)	26	4300 (16,277.3)	583 (264.4)
8748	30 x 50 (9.1 x 15.2)	28	5600 (21,198.3)	683 (309.8)
8749	50 x 50 (15.2 x 15.2)	36	10000 (37,854.1)	1,006 (456.3)

Rebar not included - 1" diameter recommended



PVC MATERIAL SPECIFICATIONS

	54 mil PVC Material	38 mil PVC Material	Testing Method
Color / Emobss	Tan / Deep Twist	Tan / Walkabout	-
Substrate	9x9 (2,000 denier) WiWk, Polyester	9x9 (2,000 denier) WiWk, Polyester	-
Overall Weight	39.8 oz./yd ²	24.2 oz./yd ²	ASTM D3776
Fabric Weight	5.0 oz./yd ²	5.0 oz./yd ²	ASTM D3776
Coating Weight	34.8 oz./yd ²	19.2 oz./yd ²	ASTM D3776
Thickness	0.060"	0.038"	-
Trapezoid Tear	Warp: 208 lbs. / Fill: 119 lbs.	Warp: 224 lbs. / Fill: 133 lbs.	ASTM D751
Tongue Tear	Warp: 275 lbs. / Fill: 246 lbs. (reference only)	Warp: 240 lbs. / Fill: 351 lbs. (reference only)	ASTM D751
Grab Tensile	Warp: 420 lbs./in / Fill: 397 lbs./in	Warp: 344 lbs./in / Fill: 363 lbs./in	ASTM D751
Adhesion	Warp: 22 lbs./in / Fill: 24 lbs./in	Warp: 15 lbs./in / Fill: 16 lbs./in	ASTM D751
Puncture Resistance			
5/16" screwdriver tip	84 lbs.	70 lbs.	ASTM D751
1" steel ball tip	491 lbs.	330 lbs.	ASTM D751
Leaks - Hydrostatic	No leaks @ 50 psi	5 samples passed 55 psi - no leaks	Vintex TM-01
Low Temp Flex	-20°C	-30°C	ASTM D2136
Abrasion	8,000 cycles	3,000 cycles	ASTM D3389 Taber, H18 wheel, 1000 g load, first sign of fabric



UltraTech International, Inc. · 11542 Davis Creek Court, Jacksonville, Florida 32256 USA
 (800) 353-1611 · 1-904-292-1611 · spillcontainment.com