



No.:

Date: 27-DEC-2012

Customer :

TECHNICAL PROPOSAL

Three-phase induction motor - Squirrel cage rotor

Product line : P-Base Motors : High Efficiency

Catalog Number : 02518EP3E284HP

List Price : \$3,451

Notes:

Performed by:

Checked:



No.:

Date: 27-DEC-2012

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : P-Base Motors : High Efficiency

Frame : 284HP
Output : 25 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1760
Slip : 2.22 %
Voltage : 208-230/460 V
Rated current : 65.5-59.2/29.6 A
Locked rotor current : 361/181 A
Locked rotor current (I_L/I_n) : 6.1
No-load current : 18.8/9.40 A
Full load torque : 73.6 lb.ft
Locked rotor torque : 230 %
Breakdown torque : 250 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 30 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000
Degree of Protection : IP55
Approximate weight : 447 lb
Moment of inertia : 4.7491 sq.ft.lb
Noise level : 68 dB(A)

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6312 C3	6211 C3	100%	0.85	92.4
Regreasing interval	10000 h	10000 h	75%	0.82	92.4
Grease amount	21 g	11 g	50%	0.74	92.4

Notes:

Performed by


Checked



No.:

Date: 27-DEC-2012

PERFORMANCE CURVES RELATED TO RATED OUTPUT Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : P-Base Motors : High Efficiency

Frame	: 284HP	Locked rotor current (I _l /I _n)	: 6.1
Output	: 25 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.25
Full load speed	: 1760	Design	: B
Voltage	: 208-230/460 V	Locked rotor torque	: 230 %
Rated current	: 65.5-59.2/29.6 A	Breakdown torque	: 250 %
Insulation class	: F		

Notes:

Performed by

Checked




No.:

Date: 27-DEC-2012

CHARACTERISTIC CURVES RELATED TO SPEED

Three-phase induction motor - Squirrel cage rotor



Customer :
Product line : P-Base Motors : High Efficiency

Frame	: 284HP	Locked rotor current (I _l /I _n)	: 6.1
Output	: 25 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.25
Full load speed	: 1760	Design	: B
Voltage	: 208-230/460 V	Locked rotor torque	: 230 %
Rated current	: 65.5-59.2/29.6 A	Breakdown torque	: 250 %
Insulation class	: F		

Notes:

Performed by

Checked

1 2 3 4 5 6 7 8

A


B

C

D

E

F



Notes:

Performed by:

Checked:

Customer:

P-Base Motors : High Efficiency

Three-phase induction motor
Frame 284HP - IP55

27-DEC-2012



ES 1.250	S 0.250	EU 0.875	U 1.125	R 0.984
P 14.094	AH 2.750	AB 10.866	C 26.350	CH 2.244
AA NPT 1 1/2"	Flange FD-254	AJ 9.125	AK 8.250	BD 10.000
BF 0.433	BB 0.196			