



No.:

Date: 28-DEC-2012

Customer :

TECHNICAL PROPOSAL

Single-phase induction motor - Squirrel cage rotor

Product line : Pool & Spa Motors : C-Face - Start Capacitor - High Service Factor

Catalog Number : PCJ105H

List Price : \$236

Notes:

Performed by:

Checked:



No.:

Date: 28-DEC-2012

## DATA SHEET

### Single-phase induction motor - Squirrel cage rotor

Customer :  
Product line : Pool & Spa Motors : C-Face - Start Capacitor - High Service Factor

Frame : K56J  
Output : 0.5 HP  
Frequency : 60 Hz  
Poles : 2  
Full load speed : 3515  
Slip : 2.36 %  
Voltage : 115/230 V  
Rated current : 9.10/4.55 A  
Locked rotor current : 53.7/26.8 A  
Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 5.9  
No-load current : 7.70/3.85 A  
Full load torque : 0.737 lb.ft  
Locked rotor torque : 210 %  
Breakdown torque : 400 %  
Design : ---  
Insulation class : B  
Temperature rise : 80 K  
Locked rotor time : 6 s (hot)  
Service factor : 1.60  
Duty cycle : S1  
Ambient temperature : -20°C - +40°C  
Altitude : 1000  
Degree of Protection : IP21  
Approximate weight : 23 lb  
Moment of inertia : 0.02326 sq.ft.lb  
Noise level : ---

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6203 2RS	6203 ZZ	100%	0.59	60.4
Regreasing interval	---	---	75%	0.52	54.0
Grease amount	---	---	50%	0.43	45.0

Notes:

Performed by


Checked



No.:

Date: 28-DEC-2012

### PERFORMANCE CURVES RELATED TO RATED OUTPUT Single-phase induction motor - Squirrel cage rotor




Customer :  
Product line : Pool & Spa Motors : C-Face - Start Capacitor - High Service Factor

Frame	: K56J	Locked rotor current (I <sub>l</sub> /I <sub>n</sub> )	: 5.9
Output	: 0.5 HP	Duty cycle	: S1
Frequency	: 60 Hz	Service factor	: 1.60
Full load speed	: 3515	Design	: ---
Voltage	: 115/230 V	Locked rotor torque	: 210 %
Rated current	: 9.10/4.55 A	Breakdown torque	: 400 %
Insulation class	: B		

Notes:

Performed by

Checked



Notes:	
Performed by:	
Checked:	
Customer:	
Pool & Spa Motors : C-Face - Start Capacitor - High Service Factor	
Single-phase induction motor Frame K56J - IP21	28-DEC-2012

P 5.748	C 13.898	AA NPT 1/2	Flange FC-149	AJ 5.874
AK 4.500	BD 5.748	BF UNC 3/8"x16	BB 0.157	BC ---
AH 2.563				

