



FAST, EFFICIENT AND RELIABLE


The INFICON QS5 Vacuum Pump is designed for quick, deep evacuation as well as affordability and durability.

QS5 is a two-stage, rotary vane pump with 5 CFM rated displacement for ultimate vacuum down to 15 microns. Features such as a large oil sightglass, easily accessible oil drain and innovative oil-trapping exhaust/demister allow technicians to make easier, more efficient service calls.

The pump's design includes a comfortable "no slip" grip for easy carrying and its solid construction delivers maximum durability. All this is backed by an industry-leading 2-year replacement warranty.

FEATURES AT A GLANCE

- Two-stage rotary vane pump provides the ability to quickly pull a deep, 15 micron vacuum
- Anti-backflow on inlet prevents oil from flowing back to the system if there's a power disruption
- Gas ballast allows pumped water vapor to be exhausted to atmosphere instead of accumulating in the oil reservoir
- Internal oil pumping design lubricates the pump chamber and bearings
- Tethered caps on oil drain and inlets so you can't drop or lose them
- Fan directs airflow for maximum heat transfer, keeping pump cooler
- Aluminum housing provides maximum durability
- Wide stance and solid base for greater stability and less chance of the pump tipping over
- Thermally protected motor ensures safe operation.



SPECIFICATIONS		
Base unit includes	110V / 220V dual voltage operation. Includes power cord, one bottle of oil and manual.	
Free Air Displacement	5 cfm (142 liters per min) (at 60 Hz)	
Motor	½ HP AC	
Oil Capacity	12.5 oz. / 370 mL	
Weight	24 lbs. / 10.89 kg	
Warranty	2 year replacement	

QS5 VACUUM PUMP / ACCESSORIES		
QS5 Pump	700-100-P1	
Replacement Parts		
Oil (6 qts/case)	071-0730	
Replacement power cord	068-0391	

