

# popcorn seating | product specification

## Stacking Chairs Models 6710, 6711, 6712 & 6714

### Dimensions

Overall Width		23.5 in / 597 mm
Overall Height		32.5 in / 826 mm
Seat Depth		18 in / 457 mm
Seat Height	6710	16.5 in / 419 mm
	6711	16.5 in / 419 mm
	6712	17 in / 432 mm
	6713	17 in / 432 mm
Back Height - From Seat	6710	16 in / 406 mm
	6711	16 in / 406 mm
	6712	15.5 in / 394 mm
	6713	15.5 in / 394 mm

### With Armrests (Models 6710 and 6712)

Overall Height		24.5 in / 622 mm
Seat Width		18 in / 457 mm
Armrest Clearance		21 in / 533 mm
Arm Height - From Seat		8 in / 203 mm
Product Weight	6710	21 lbs / 9.5 kgs
	6712	22 lbs / 10.0 kgs
Shipping Weight	6710	94 lbs / 42.7 kgs
	6712	98 lbs / 44.5 kgs
Shipping Cube	6710	17.75 ft <sup>3</sup> / 0.50 m <sup>3</sup>
	6712	19.25 ft <sup>3</sup> / 0.54 m <sup>3</sup>

### Without Armrests (Models 6711 and 6713)

Overall Height		20 in / 508 mm
Seat Width		18 in / 457 mm
Product Weight	6711	15 lbs / 6.8 kgs
	6713	16 lbs / 7.3 kgs
Shipping Weight (4 per carton)	6711	69 lbs / 31.4 kgs
	6713	73 lbs / 33.2 kgs
Shipping Cube	6711	14.75 ft <sup>3</sup> / 0.42 m <sup>3</sup>
	6713	16 ft <sup>3</sup> / 0.45 m <sup>3</sup>

Contact sales rep for more information.

### Features

- Sled base
  - No crossbar on base that might interfere with legs of feet
  - Leg design prevents chair back from damaging walls
  - Seat pan has waterfall edge to help maintain proper leg circulation
  - Designed to be easily moved via a hand-hold pass through located on top edge of chair
  - Seating shipped fully assembled
- MODELS 6710 & 6712
- Integrated arms match shell colour
- MODELS 6710 & 6711
- Stacks up to 10 high on floor or 34 high on chair dolly
- MODELS 6712 & 6713
- Stacks up to 8 high on floor or 15 high on chair dolly



6710



6711



6712



6713



# popcorn seating | product specification

## Options

- Chair shell available in 10 versatile colours
- Two clear non-marking glides are available for hard or sensitive flooring
- Ganging clamps are available for linking chairs. No clearance between chairs with armrests. 6 in (152 mm) clearance between chairs without armrests

## Construction (Frame)

- Solid steel rod with chrome finish
  - 0.5 in (13 mm) diameter
- MODELS 6712 & 6713
- Polypropylene shroud on underside of seat frame prevents imprints or damage to other chairs when stacked

## Construction (Seat and Back)

Molded, single piece, polypropylene shell.

## Construction (Arms)

MODELS 6710 & 6712

- Fiberglass reinforced cantilever nylon arms
- Cantilever design allows freedom of movement and accommodates larger users

## Construction (Glides)

- Full length polypropylene glides
- Glides are translucent and non-marking
- Glides can be removed for ease of movement on carpeted flooring

## Upholstery

MODELS 6710 & 6711

- Seat can be upholstered in fabric, vinyl, or leather

## Foam (Seat)

MODELS 6712 & 6713

- 0.75 in (19 mm) thick foam
- Density: 1.5 lbs, ILD: 70

## Weight Capacity

Designed for a static load of 1000 lbs and an active weight capacity of 300 lbs per seat.

## Warranty

Lifetime warranty on all components except the following:

- 5 year warranty on foams and fabrics
- 12 year warranty on control mechanisms
- Warranty applies only to single shift, standard commercial usage (8 hours/day, 5 days/week)

## Fire Rating

All fabric and foam is tested and certified, meeting CAL 117 standards. Chair may meet CAL 133 requirements with certain upholstery selections.

## Environmental

View [Environmental Data Sheets](#) online. All foam is produced without using any ozone depleting chloro-flouro chemicals.

## Awards/Certifications

- Meets or exceeds all applicable BIFMA standards for safety and durability
- Manufactured in ISO 9001 and 14001 certified facilities
- Greenguard Gold (Indoor Air Quality)
- level® e3 Sustainability Certified: Level 3

