



DASH NO.	"C"	"AD"
438	10.38	6.62
488	10.88	7.12
538	11.38	7.62
588	11.88	8.12
638	12.38	8.62

CLASS I, GROUP C & D
 CLASS II, GROUP F & G
 MAXIMUM FACE RUNOUT .004 T.I.R.
 MAXIMUM PILOT ECCENTRICITY .004 T.I.R.
 PERMISSIBLE SHAFT RUNOUT .002 T.I.R.

		TOLERANCES UNLESS SPECIFIED		LEESON	ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN BJB 06/09/03	
		DEC.	INCHES			CHK	APPD
		.X	±.1	TITLE		SCALE	1=2
		.XX	±.03	OUTLINE 56 FRAME T.E.N.V. - "C" FACE		REF	
		.XXX	±.005	MAT'L.		FMF	
		.XXXX	±.0005	EXPLOSION PROOF		PREV	
NO.	REVISION	BY & DATE	CHK	ANG	FINISH		
			RFP		CAD FILE	028516	SIZE B
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				DIST	DRAWING NO. 028516		REV.