

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings LC6, LI6, L7X, L7XR, LI6F, L7XF and L7XFR.

CONSTRUCTION

All finishes are one-piece aluminum open reflectors with integral flange.

INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.

LISTING


UL Listed to U.S. and Canadian safety standards.

Damp location listed.

6" Full Reflector Trim


6B1

PREMIUM BAFFLE
Wide Flange



Specifications

Height: 6-1/2 (16.5)
Lamp opening: 4-5/8 (11.7)
Diameter: 7-5/8 (19.4)
Trim height when used with
Non-IC incandescent rough-in



All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **6B1 TOR**

6B1	
Series	Finish
6B1	(blank) Black baffle W White baffle BN Brushed nickel reflector with black baffle ¹

TOR
Mounting method
TOR Torsion springs

NOTES:

1 Flange matches trim finish.

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30	LC6, LI6, L7X, L7XR
		40 A19	LC6, LI6, L7X, L7XR
Non-IC	Fluorescent	13DTT	L7XF
		18DTT	L7XF, LI6F, L7XFR
		26TRT	LI6F, L7XF, L7XFR
		32TRT	LI6F
		18TRT	L7XF, L7XFR

6B1 6" Premium Baffle Full Reflector Trim



Sheet #: 6B1-TOR

©2009 Acuity Brands Lighting, Inc., 8/17/09

Lithonia Lighting
Recessed Downlighting
One Lithonia Way, Conyers, GA 30012
Phone: 800-315-4935 Fax: 770-918-1209
www.lithonia.com