

### Standard Features:

- Guillotine cutter accurately cuts through paper stacks up to 2.15" high, up to 16.9" wide
- LED Laser cut line for pinpoint accuracy
- High-quality steel blade
- Front and rear safety covers
- Manual lever cutting arm
- Geared clamping system
- Spindle-guided back gauge crank
- Calibrated scale for fine adjustments, in both inches and metric
- Common paper sizes clearly marked
- Solid steel blade carrier
- Wooden paper push for safe alignment
- All-metal stand and tabletop feet included
- Blade depth adjustment from outside machine
- Easy blade change access from front of machine
- Blade change safety tool included

### Supplies:

- 15M-10: Replacement Blade
- 15M-20: Replacement Cutting Sticks, pkg of 8



Shown with stand, included

The Formax **Cut-True 15M Manual Paper Cutter** features a hardened steel blade to easily slice through paper stacks up to 2.15" high. Its Guillotine blade and LED Laser Line combine to offer precision cutting with minimal effort. Simply load a stack of paper, up to 16.9" wide, secure with the geared clamp, and pull down on the lever arm; it's that easy.

Using the spindle-guided back gauge and calibrated scales, operators can make fine adjustments, while the Laser Line shows exactly where to cut.

In addition to accuracy, the Cut-True 15M has a range of safety features including front and rear transparent covers, blade lock, external blade depth adjustment, easy-to-use blade change safety tool, and a wooden paper push for safe alignment. This compact model also includes a rugged all-metal stand, plus feet for tabletop use.

The Cut-True 15M is ideal for transforming brochures, invitations and more, with crisp, accurate cuts.

### Specifications:

Cutting Action:	Manual lever handle
Maximum Cutting Width:	16.9" (430mm)
Maximum Paper Stack Height:	2.15" (55mm)
LED Laser Cut Line:	Yes
Clamp Style:	Spindle-guided clamping wheel
Back Gauge Adjustment:	Manual crank
Back Gauge Reading:	Scale, in both inches and metric
Blade Change Safety Tool:	Included
Dimensions:	42.5" H x 26.8" W x 29.1" D (1080 H x 680 W x 740 D mm)
Weight:	133 lbs. (60kg)
Safety Certifications:	CE approved

Cut-True Cutters