

When to offer CMW Systems

CMW (is compatible with Steelcase™ Avenir® design)

- CMW panels are acoustical and tackable as a standard
- CMW panels come with USA Byrne Electric (newest and safest technology vs Asian post patent copied electrical system). Electrical system comes with a 10 year warranty and \$5MM liability coverage.
- CMW is made to BIFMA and UL specifications.
- CMW products are painted with powder coat material using a DuPont formula to reduce nicks and scratches.
- CMW is GSA approved and made in the USA.
- CMW comes with a lifetime warranty for component parts. Note 5 years on moveable parts and 3 years on fabric.
- CMW panel electrical is designed with patented snap-in wire harnesses for easy installation.
- CMW Panels offer a Patent-Pending "PolyStax design" allowing the system to be easily field expanded from one height to another height all the way up to standard ceiling height and therefore offering a floor-to-ceiling office design option.
- CMW PolyStax stackers are available in 5 heights and 6 widths and come in fabric, laminate, frosted, smoked, and clear acrylic, as well as whiteboard options.
- Universal single design panel to panel hardware connection.
 1. No additional parts (e.g. connectors of varying heights and shapes)
 2. All panel to panel angles are possible which is better for re-purposing
- Panel base raceway is flush which is a more current modern design
- Panel to panel drop height connector is simple steel connection – not a plastic variable height strip.
- Flush raceway is metal versus textured plastic for quality impression
- Flush Raceway nests against wall as opposed to bulbous base of AO
- CMW comes with full height doors and sliding doors