


108232.00	16.82	14.76	8.46	180	1 1/2	1750
108231.00	14.82	12.76	6.46	180	1	1750
108230.00	14.82	12.76	6.46	90	1	1750
<b>CATALOG No.</b>	<b>"C"</b>	<b>"L"</b>	<b>"AD"</b>	<b>VOLTS</b>	<b>H.P.</b>	<b>RPM</b>

- NOTES:  
 1) MAXIMUM FACE RUNOUT .004 T.I.R.  
 2) MAXIMUM PILOT ECCENTRICITY .004 T.I.R.  
 3) PERMISSIBLE SHAFT RUNOUT .002 T.I.R.  
 4) GASKETS THROUGHOUT.

			TOLERANCES UNLESS SPECIFIED		 <b>ELECTRIC MOTORS GEARMOTORS AND DRIVES</b>		DRAWN IPG 1/30/09	
02	ADDED NOTE ABOUT FAN GUARD FLAT LOCATION. ISAAC 09-4813	IPG 12/10/2009	DEC	INCHES			CHK SK 1/30/09	
01	CAT. # 108232.00: "C" WAS 17.32, "L" WAS 15.26, "AD" WAS 8.96. ISAAC 09-1828	IPG 5/14/2009	SK XX	±.03	TITLE OUTLINE	SCALE 1:2		
	RELEASED: REF. 030967 & 031900	IPG 1/30/2009	SK XXX	±.005	48 FRAME DC	REF 030967		
			SK XXXX	±.0005	MATL	FMF 108230.75		
REVISION			BY & DATE	CHK ANG ±1/2°	FINISH	PAGE OF		
THIRD ANGLE PROJECTION			RFP	PREV	SIZE	DRAWING NO	REV	
			NETWORK FILE NAME		<b>B</b>	<b>031909</b>	<b>02</b>	